



OPTRIS CSlaser LT INFRARED PYROMETER, -30-1000 DEG C, 8-14  $\mu$ m SPECTRAL RANGE, 4-20mA AND ALARM OUTPUT, 5-30 VDC OPERATING VOLTAGE, M48x1.5 THREADED END MOUNT, REMOVABLE SCREW TERMINAL PLUG

**OPTCSLLTSF**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
**[inch]**

LATEST VERSION  
7/18/2023

SHEET 1 OF 1