



OPTRIS CSmicro 2M INFRARED PYROMETER, 385-1600 DEG C, 1.6 µm SPECTRAL RANGE, 4-20mA ALARM OR PULSE OUTPUT, 5-30 VDC OPERATING VOLTAGE, M12x1 THREADED END MOUNT, 6m INTEGRAL 5-CONDUCTOR SHIELDED CABLE

**OPTCSMA2MHSF33**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

mm  
[inch]

LATEST VERSION  
7/18/2023

SHEET 1 OF 1