



OPTRIS CSmicro 3M INFRARED PYROMETER, 50-350 DEG C, 2.3 µm SPECTRAL RANGE, 0-5 VDC, 0-10 VDC, ALARM OR PULSE OUTPUT, 5-30 VDC OPERATING VOLTAGE, M12x1 THREADED END MOUNT, 1m INTEGRAL 5-CONDUCTOR SHIELDED CABLE

**OPTCSMV3MLSF0505**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
7/18/2023

SHEET 1 OF 1