



OPTRIS CSmicro 3M INFRARED PYROMETER, 50-350 DEG C, 2.3 µm SPECTRAL RANGE, 0-5 VDC, 0-10 VDC, ALARM OR PULSE OUTPUT, 5-30 VDC OPERATING VOLTAGE, M12x1 THREADED END MOUNT, 6m INTEGRAL 5-CONDUCTOR SHIELDED CABLE

OPTCSMV3MLSF33

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
7/18/2023

SHEET 1 OF 1