



- 1.) INPUT +/-
- 2.) OUTPUT +/-, 24VDC BUFFERED
- 3.) LED RED: ALARM
LED YELLOW: CHARGE / BUF. MODE
LED GREEN: DC OK
- 4.) SIGNAL CONTACT
13 = POTENTIAL-FREE SUMMATION INPUT FOR 14/24
14 = UPS WORKS IN BUFFER MODE
24 = CAPACITOR VOLTAGE < 85%



ISOMETRIC VIEW



BLOCK-DC UPS POWER SUPPLIES

PC-0424-010-00

AutomationDirect.com
1-800-633-0405

3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE: mm [inch]	MODEL REV. --	DRAWING DATE 1/23/2026	SHEET 1 OF 1
-----------	--------------	---	-----------------------------------	--	----------------------	---------------------------	--------------