



PUSHBUTTON, 40A, 3-POLE, 480 VAC (50/60Hz) COIL VOLTAGE, THERMAL OVERLOAD, 25.0-40.0A ADJUSTABLE, NEMA 4/4X.

WEG ELECTRIC MANUAL MOTOR STARTER

PESW-B40D39AX-R70

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
1/18/2023

SHEET 1 OF 1