



2-PORT (2-WAY), 2-POSITION, N.C., BRASS BODY, VITON SEAL(s), 1/2IN FEMALE NPT INLET(s), 1/2IN FEMALE NPT OUTLET(s), CV=4.3, 0 PSI MINIMUM OPERATING PRESSURE, 120 VAC OPERATING VOLTAGE, 18mm DIN STYLE WIRING PLUG.

## GC VALVES SOLENOID VALVE

**S201YH02V5DG4**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR  
PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**inch**  
**[mm]**

LATEST VERSION  
12/15/2025

SHEET 1 OF 1