



2-PORT (2-WAY), 2-POSITION, N.C., BRASS BODY, NITRILE SEAL(S), 1/2IN FEMALE NPT INLET(S), 1/2IN FEMALE NPT OUTLET(S), CV=4.3, 0 PSI MINIMUM OPERATING PRESSURE, 24 VDC OPERATING VOLTAGE, 18mm DIN STYLE WIRING PLUG.

GC VALVES SOLENOID VALVE

S201YH16N5DG4

AutomationDirect.com
1-800-633-0405

<p>3rd ANGLE</p>	<p>NOT TO SCALE</p>	<p>PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES</p>	<p>INCH UNITS USED FOR PART DESIGN</p>	<p>UNLESS OTHERWISE SPECIFIED UNITS ARE: inch [mm]</p>	<p>LATEST VERSION 12/15/2025</p>	<p>SHEET 1 OF 1</p>
------------------	---------------------	--	--	---	--------------------------------------	---------------------