



2-PORT (2-WAY), 2-POSITION, N.C., BRASS BODY, NITRILE SEAL(s), 1IN FEMALE NPT INLET(s), 1IN FEMALE NPT OUTLET(s), CV=13, 5 PSI MINIMUM OPERATING PRESSURE, 120 VAC OPERATING VOLTAGE, 18mm DIN STYLE WIRING PLUG.

**GC VALVES SOLENOID VALVE**

**S211YH02N5FG9**

AutomationDirect.com  
1-800-633-0405

3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	INCH UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	inch [mm]	LATEST VERSION 12/15/2025	SHEET 1 OF 1
-----------	--------------	---	---------------------------------	---------------------------------------	-----------	---------------------------	--------------