



2-PORT (2-WAY), 2-POSITION, N.C., BRASS BODY, NITRILE SEAL(s), 3/8IN FEMALE NPT INLET(s), 3/8IN FEMALE NPT OUTLET(s), CV=4.3, 4 PSI MINIMUM OPERATING PRESSURE, 24 VDC OPERATING VOLTAGE, 18mm DIN STYLE WIRING PLUG.

GC VALVES SOLENOID VALVE

S211YH16N5CG4

AutomationDirect.com
1-800-633-0405

3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	INCH UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE: inch [mm]	LATEST VERSION 12/15/2025	SHEET 1 OF 1
-----------	--------------	---	---------------------------------	--	------------------------------	--------------