



2-PORT (2-WAY), 2-POSITION, N.C., BRASS BODY, NITRILE SEAL(s), 1/2IN FEMALE NPT INLET(s), 1/2IN FEMALE NPT OUTLET(s), CV=4.3, 4 PSI MINIMUM OPERATING PRESSURE, 24 VDC OPERATING VOLTAGE, 18mm DIN STYLE WIRING PLUG.

GC VALVES SOLENOID VALVE

S211YH16N5DG4

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
12/15/2025

SHEET 1 OF 1