



2-PORT (2-WAY), 2-POSITION, N.C., BRASS BODY, NITRILE SEAL(S), 3/4IN FEMALE NPT INLET(S), 3/4IN FEMALE NPT OUTLET(S), CV=6.7, 4 PSI MINIMUM OPERATING PRESSURE, 24 VDC OPERATING VOLTAGE, 18mm DIN STYLE WIRING PLUG

**GC VALVES SOLENOID VALVE**

**S211YH16N5EG5**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR  
PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**inch**  
**[mm]**

LATEST VERSION  
12/15/2025

SHEET 1 OF 1