



2-PORT (2-WAY), 2-POSITION, N.C., BRASS BODY, VITON SEAL(s), 1/4IN FEMALE NPT INLET(s), 1/4IN FEMALE NPT OUTLET(s), CV=0.65, 0 PSI MINIMUM OPERATING PRESSURE, 120 VAC OPERATING VOLTAGE, 18mm DIN STYLE WIRING PLUG.

GC VALVES SOLENOID VALVE

S301YH02V8BE1

AutomationDirect.com
1-800-633-0405

| | | | | | | | | |
|--|-----------|--------------|---|---------------------------------|---------------------------------------|-----------|---------------------------|--------------|
| | 3rd ANGLE | NOT TO SCALE | PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES | INCH UNITS USED FOR PART DESIGN | UNLESS OTHERWISE SPECIFIED UNITS ARE: | inch [mm] | LATEST VERSION 12/15/2025 | SHEET 1 OF 1 |
|--|-----------|--------------|---|---------------------------------|---------------------------------------|-----------|---------------------------|--------------|