



2-PORT (2-WAY), 2-POSITION, N.C., STAINLESS STEEL BODY, VITON SEAL(s), 1/4IN FEMALE NPT INLET(s), 1/4IN FEMALE NPT OUTLET(s), CV=0.14, 0 PSI MINIMUM OPERATING PRESSURE, 24 VDC OPERATING VOLTAGE, 11mm DIN STYLE WIRING PLUG.

**CFA SOLENOID VALVE**

**SC911YH16VFBA5**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR  
PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**inch**  
**[mm]**

LATEST VERSION  
12/15/2025

SHEET 1 OF 1