



2-PORT (2-WAY), 2-POSITION, N.O., STAINLESS STEEL BODY, VITON SEAL(s), 1/8IN FEMALE NPT INLET(s), 1/8IN FEMALE NPT OUTLET(s), CV=0.086, 0 PSI MINIMUM OPERATING PRESSURE, 120 VAC OPERATING VOLTAGE, 11mm DIN STYLE WIRING PLUG.

**CFA SOLENOID VALVE**

**SC912YH02VFAA5**

AutomationDirect.com  
1-800-633-0405

<p>3rd ANGLE</p>	<p>NOT TO SCALE</p>	<p>PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES</p>	<p>INCH UNITS USED FOR PART DESIGN</p>	<p>UNLESS OTHERWISE SPECIFIED UNITS ARE: <b>inch [mm]</b></p>	<p>LATEST VERSION 12/15/2025</p>	<p>SHEET 1 OF 1</p>
------------------	---------------------	--	--	---	--------------------------------------	---------------------