



3-PORT (3-WAY), 2-POSITION, N.C., BRASS BODY, VITON SEAL(s), 1/4IN FEMALE NPT INLET(s), 1/4IN FEMALE NPT OUTLET(s), CV=0.084, 0 PSI MINIMUM OPERATING PRESSURE, 24 VAC OPERATING VOLTAGE, 11mm DIN STYLE WIRING PLUG.

CFA SOLENOID VALVE

SC913YH24VEBA3

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
12/15/2025

SHEET 1 OF 1