



120 VAC OPERATING VOLTAGE, DAYLIGHT WHITE, 5000K, 19.5W,
BRACKET MOUNT, PIGTAIL, ANODIZED ALUMINUM BODY, 9.8FT/3M
CABLE LENGTH, IP67. MOUNTING BRACKET INCLUDED.

CCEA TRACKALPHA-PRO LED LIGHT BAR

TA0324S0203

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
10/23/2023

SHEET 1 OF 1