



M12 X 1.5MM THREAD TYPE, POLYAMIDE, LIGHT GRAY, 5000 ML/MIN @ 70 mbar (1 PSI), IP66 IP68, UL TYPE 4X. PACKAGE OF 2.

TIGHTENING TORQUE: 0.5 ± 0.1Nm (4 ± 1ft·lbs)

BIMED PRESSURE RELIEF VENT PLUG

UHBVPB-11L-WNL

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
5/20/2024

SHEET 1 OF 1