






Ø 12.5
[0.49]
KNOCK-OUT
(1X) TOP SIDE

Ø 20.5
[0.81]
KNOCK-OUTS
(5X) TOP SIDE

ISOMETRIC VIEW



Ø 20.5
[0.81]
KNOCK-OUTS
(2X) LEFT SIDE



Ø 50.5
[1.99]
KNOCK-OUT
(1X) BOTTOM


Ø 16.5
[0.65]
KNOCK-OUT
(1X) BOTTOM

Ø 12.5
[0.49]
KNOCK-OUT
(2X) BOTTOM

FIBOX MNX ENCLOSURES

ULPCM150150XG

AutomationDirect.com
1-800-633-0405

	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	mm [inch]	MODEL REV.	DRAWING DATE 10/24/2025	SHEET 1 OF 1
--	--------------	-----------------	--	--------------------------------------	--	--------------	---------------	----------------------------	--------------