






25.0
[0.98]
TYP.

Ø 20.5
[0.81]
KNOCK-OUTS
(2X) TOP &
(2X) BOTTOM



Ø 32.5
[1.28]
KNOCK-OUTS
(2X) TOP &
(2X) BOTTOM

ISOMETRIC VIEW



Ø 16.5
[0.65]
KNOCK-OUTS
(3X) LEFT SIDE
(3X) RIGHT SIDE

Ø 25.5
[1.00]
KNOCK-OUTS
(3X) LEFT SIDE
(3X) RIGHT SIDE



FIBOX MNX ENCLOSURES

ULPCM15060G

AutomationDirect.com
1-800-633-0405

3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE: mm [inch]	MODEL REV. --	DRAWING DATE 10/23/2025	SHEET 1 OF 1
--------------	-----------------	--	--------------------------------------	--	-------------------------	----------------------------	--------------