




Model: FBP-LN-0E



Made in Germany

Polarized retro-reflective sensor



voltage: 10...30 V DC IP 67
out max: 200 mA NPN (light-on)
range: 0.05...2.5 m

The device shall be supplied from an isolating transformer having a secondary Listed fuse rated either
a) max 5 amps for voltages 0~20 Vrms (0~28.3 Vp) or
b) 100/Vp for voltages of 20~30 Vrms (28.3~42.4 Vp).

Qty:



1



TAA0411



FBP-LN-0E