



AUTOMATIONDIRECT.com

Model: FBP-LP-0E



Made in Germany

Polarized retro-reflective sensor



voltage:	10...30 V DC	IP 67
out max:	200 mA PNP (light-on)	
range:	0.05...2.5 m	

The device shall be supplied from an isolating transformer having a secondary Listed fuse rated either
a) max 5 amps for voltages 0~20 Vrms (0~28.3 Vp) or
b) 100/Vp for voltages of 20~30 Vrms (28.3~42.4 Vp).

Qty:

1

TAA0411

FBP-LP-0E