




AUTOMATIONDIRECT.com

Model: FBR-LN-0E



Made in Germany

Through-beam sensor, receiver



voltage:	10...30 V DC	IP 67
out max:	200 mA NPN (light-on)	
range:	0...8 m	

The device shall be supplied from an isolating transformer having a secondary Listed fuse rated either
a) max 5 amps for voltages 0~20 Vrms (0~28.3 Vp) or
b) 100/Vp for voltages of 20~30 Vrms (28.3~42.4 Vp).

Qty: 1

TAA0411

FBR-LN-0E