

# REPLACEMENT PARTS

---





# CHAPTER 9

## In This Chapter...

Replacement Parts Overview .....	9-2
3-wire Communications Terminal Block – EA9-3TB.....	9-3
DC Panel Power Connector Replacement – C0-4TB.....	9-3

## Replacement Parts Overview

Part Number		Description
EA9-3TB		<p><b>C-more</b> pluggable terminal block, replacement, 3-pole. Package of 2. For use with 3-wire RS485 communications port on <b>C-more</b> EA9 series panels.</p>
C0-4TB		<p>CLICK terminal blocks, replacement, 4-pole. Package of 2. For use with CLICK PLCs and <b>C-more</b> EA9-RHMI.</p>

## 3-wire Communications Terminal Block – EA9-3TB


*C-more* EA9 series 3-wire communications terminal block replacement. One (1) terminal block is supplied with each HMI. Two (2) connectors are supplied when ordered as a replacement part.



Tightening Torque	
Cable torque	Minimum 1.95 lb-in (0.22 Nm)



**NOTE:** Use 60/75 °C copper conductors only, 24-12 AWG



9

## DC Power Connector Replacement – C0-4TB

EA9-RHMI 4-position DC power connector terminal block replacement. One (1) DC Power Connector is supplied with each HMI. Two (2) connectors are supplied when ordered as a replacement part.



Tightening Torque	
Power supply cable torque	32-35 oz-in (0.22- 0.25Nm)



**NOTE:** Use 60/75 °C copper conductors only, 24-12 AWG

