

FLL-C3006UITB

AC lamps

> CONTATTACI



The FLL series LED lamps ensure low energy consumption, less than 5W, and optimal illumination of electrical panels thanks to high-quality lens and a brightness of 600 lumen. They are available with a wide range supply of 20 and 230 V AC/DC and a quick electrical connection by screwless wiring system. These lamps can be swivelled to better distribute the light beam, they can be easily fixed by screws or magnetic fastening and are equipped with ON/OFF switch or motion sensor.

Technical data		
APPROVALS		
Approvals	CE; cURus; UKCA	
ELECTRICAL DATA		
Rated Voltage	20-230	V a.c./d.c.
Rated Power	5	W
Operating Voltage	20-265	V a.c./d.c.
Frequency	50/60	Hz
Appliance Class	II	
GENERIC DATA		
Lamp Type	LED	
Casing Material	PC UL94 V-0	
RAL Number	7035	
Life Expectancy	160000	h at 25 °C
	160000	h at 77 °F
Electrical Connection	Screwless Terminal Block	
Wires Section	0.5-1.5	mm²
Wires Section	20-14	AWG
Angle of Radiation PIR	120	°
Auto Switch Off	300	s
Light Cover	Polycarbonate	
Fixing System	Screws	
Switch	PIR Sensor	

Image is for illustrative purpose only. All specifications, data and drawing are subject to change without notice. Please refer to our terms of sales including our warranty and limited liabilities cla

FLL-C3006UITB

AC lamps

> CONTATTACI

ELECTRO-TECHNICAL SYSTEMS

Technical data		
PHOTOMETRIC DATA		
Color Temperature	6000	K
Light Beam Angle	120	°
Luminous Flux	600	lm
ENVIRONMENTAL AND THERMAL DATA		
IP Protection Degree	IP20	
Operating Temperature	-30÷75	°C
	-22÷167	°F
Storage Temperature	-40÷85	°C
	-40÷185	°F
UL DATA		
UL File Number Recognized Component	E237844	
UL Surrounding Temperature	60	°C
	140	°F

Image is for illustrative purpose only. All specifications, data and drawing are subject to change without notice. Please refer to our terms of sales including our warranty and limited liabilities cla

FLL-C3006UITB

AC lamps

> CONTATTACI

ELECTRO-TECHNICAL SYSTEMS




Image is for illustrative purpose only. All specifications, data and drawing are subject to change without notice. Please refer to our terms of sales including our warranty and limited liabilities cla