



The FLL series LED lamps ensure low energy consumption, less than 5W, and optimal illumination of electrical panels thanks to high-quality lens and a brightness of 600 lumen. They are available with a wide range supply of 20 and 230 V AC/DC and a quick electrical connection by screwless wiring system. These lamps can be swivelled to better distribute the light beam, they can be easily fixed by screws or magnetic fastening and are equipped with ON/OFF switch or motion sensor.

Technical data		
APPROVALS		
Approvals	UL pending; CE; UKCA	
ELECTRICAL DATA		
Rated Voltage	20-230	V a.c./d.c.
Rated Power	5	W
Operating Voltage	20-265	V a.c./d.c.
Frequency	50/60	Hz
Appliance Class	II	
GENERIC DATA		
Lamp Type	LED	
Casing Material	PC UL94 V-0	
RAL Number	7035	
Life Expectancy	160000	h at 25 °C
	160000	h at 77 °F
Electrical Connection	Screwless Terminal Block	
Wires Section	0.5-1.5	mm ²
Wires Section	20-14	AWG
Light Cover	Polycarbonate	
Fixing System	Screws	
Switch	Manual ON/OFF	
PHOTOMETRIC DATA		
Color Temperature	7100	K

Image is for illustrative purpose only. All specifications, data and drawing are subject to change without notice. Please refer to our terms of sales including our warranty and limited liabilities cla

FLL-C3006USTB

AC lamps

> CONTATTACI

Technical data		
Light Beam Angle	120	°
Luminous Flux	600	lm
ENVIRONMENTAL AND THERMAL DATA		
IP Protection Degree	IP20	
Operating Temperature	-30÷60	°C
	-22÷140	°F
Storage Temperature	-40÷85	°C
	-40÷185	°F

Image is for illustrative purpose only. All specifications, data and drawing are subject to change without notice. Please refer to our terms of sales including our warranty and limited liabilities cla

FLL-C3006USTB

AC lamps

> CONTATTACI




Image is for illustrative purpose only. All specifications, data and drawing are subject to change without notice. Please refer to our terms of sales including our warranty and limited liabilities cla