


Monitor Holder Part# 162895 Assembly Procedure



Copyright 2023, Automationdirect.com Incorporated/
All Rights Reserved Worldwide

Hardware Included

2X – Button Head
Socket Cap Screw
M6-1.0 x 16mm

2X – Button Head
Socket Cap Screw
M6-1.0 x 20mm

2X – Button Head
Socket Cap Screw
1/4-20 x 1/2"

2X – Concrete Anchor
M8 x 50mm

2X – Cable-Tie 200mm long

4X – Button Head
Socket Cap Screw
M4-0.7 x 12mm

4X – Button Head
Socket Cap Screw
M4-0.7 x 20mm

1X – Allen Wrench,
5mm

4X – Spacer, OD=9mm,
ID=5mm, Length=8mm

2X – Cross Head Screw
M6 x 60mm

2X – Roll-in T-Nut,
Slot size 10, 45 series
M6-1.0 thread


2X – Roll-in T-Nut,
Slot size 8, 30 series,
M6-1.0 thread

2X – Roll-in T-Nut,
Slot size 8, 15/40 series
M6-1.0 thread

2X – Roll-in T-Nut,
Slot size 6, 10 series
1/4-20 thread

VESA Mounting Standard

- ☑ 100 X 100mm
- ☑ 75 X 75mm
- ☑ 4X M4-0.7 Threaded Holes



100

75

2-15