

ERM AND ERM WORKBENCH DEFAULT SETTINGS



In This Appendix...

ERM and ERM Workbench Factory Default SettingsC-2

ERM and ERM Workbench Factory Default Settings

The following factory default settings or values can be changed by using the tools within the ERM Workbench utility.

C

Item	Default
Protocol	IPX
Address Mode	Ethernet Address
ERM Timeout to Slave	25ms
ERM Retries	1
Slave Watchdog	250ms
ERM Pet Slave Watchdog	0 (disabled)
ERM Consecutive Comm Failures to Slave Before Placing Slave in Standby Mode	5
Slave Padding	0
Bit Input Address	DirectLOGIC: V40414 (X300); Do-more: (DLX300)
Bit Output Address	DirectLOGIC: V50514 (Y300) Do-more: (DLY300)
Word Input Address	DirectLOGIC: V2000 Do-more: DLV2000
Word Output Address	DirectLOGIC: V2100 Do-more: DLV2100
Standby Cycle Time	500ms
Unsupported Slave Cycle Time	1000ms
PLCScan Timeout	100ms