



# Errata Sheet

This Errata Sheet contains corrections or changes made after the publication of this manual.

**Product Family:** DirectLOGIC PLCs

**Date:** September 2018

**Manual Number:** HX-ECOM-M

**Revision and Date:** 3rd Edition; Rev. C June 2011

## Change to Chapter 2. Setup and Installation

Page 2-8. Inserting the ECOM Module in the PLC Base; DL205 Slot Choices

Add the following note just below the table at the top of the page:

“Note: Also compatible with obsolete bases D2-0xB, D2-0xBDC-1 and D2-0xBDC-2.”

## Change to Chapter 5. MODBUS TCP for H0/H2/H4-ECOM100

Page 5-2. MODBUS TCP;

Add the following NOTE after the first paragraph on this page:



**NOTE:** You must configure the peer to peer configuration as shown in Chapter 3 (page 3-10) to use Modbus TC/P. If the peer to peer configuration is not configured the ECOM100 will use Host Protocol instead of Modbus TC/P.

Page 5-15. Network Client (master) Operation; MODBUS Function Codes Supported

Replace the table near the bottom of the page with this one:

ECOM100 AS MODBUS TCP CLIENT					
PLC Instruction	Operand	Modbus		FC	Description
		Base	Offset		
RX	GY0-GY3777	00000	1-2048	01	Read Coils
	Y0-Y1777		2049-3072		
	C0-C3777		3073-5120		
	S0-S1777		5121-6144		
	T0-T377		6145-6400		
	CT0-CT377		6401-6656		
	GX0-GX3777	10000	1-2048	02	Read Inputs
	X0-X1777		2049-3072		
	SP0-SP777		3073-3584		
	V0-V41117	40000	1-16976	03	Read Holding Registers
	V41140-V41157		16993-17008		
	V41200-V41237		17025-17056		
WX	GY0-GY3777	00000	1-2048	15	Force Multiple Coils
	Y0-Y1777		2049-3072		
	C0-C3777		3073-5120		
	S0-S1777		5121-6144		
	T0-T377		6145-6400		
	CT0-CT377		6401-6656		
	GX0-GX3777	10000	1-2048	-	-
	X0-X1777		2049-3072		
	SP0-SP777		3073-3584		
	V0-V41117	40000	1-16976	16	Preset Multiple Registers
	V41140-V41157		16993-17008		
	V41200-V41237		17025-17056		
	V0-V41117 (odd length)	30000	1-16976	-	-
	V41140-V41157 (odd length)		16993-17008		
	V41200-V41237 (odd length)		17025-17056		