

Do not adjust cell heights or widths for printing

PHOX Drive

APCS-PHOX-IOT-AD Terminal Designations for use with PHOX servos

- 1) Print this page with no scaling
- 2) Measure the ruler image below to verify the printed scale
- 3) Adjust your print scaling and print again if necessary
- 4) Choose one of the templates below (left template is more useful)
- 5) Cut *inside* the dotted lines below
- 6) Fold on the red line and insert into terminal block cover



PF+	PHOX	PF+	PHOX
1	PF-	1	PF-
PR+	2	PR+	2
3	PR-	3	PR-
AGND	4	AGND	4
5	AI+	5	AI+
AI-	6	AI-	6
7	AMON1	7	AMON1
AMON2	8	AMON2	8
9	DICOM	9	DICOM
DI1	10	DI1	10
11	DI2	11	DI2
DI3	12	DI3	12
13	DI4	13	DI4
DO1	14	DO1	14
15	DO2	15	DO2
DO3	16	DO3	16
17	DO4	17	DO4
AO	18	AO	18
19	/AO	19	/AO
BO	20	BO	20
21	/BO	21	/BO
ZO	22	ZO	22
23	/ZO	23	/ZO
DOCOM	24	DOCOM	24
25	AGND	25	AGND
PHOX	26	PHOX	26

A1	PHOX	PF+	PHOX
1	B1	1	PF-
A2	2	PR+	2
3	B2	3	PR-
A3	4	AGND	4
5	B3	5	AI+
A4	6	AI-	6
7	B4	7	AMON1
A5	8	AMON2	8
9	B5	9	DICOM
A6	10	DI1	10
11	B6	DI2	11
A7	12	DI3	12
13	B7	DI4	13
A8	14	DO1	14
15	B8	DO2	15
A9	16	DO3	16
17	B9	DO4	17
A10	18	AO	18
19	B10	/AO	19
A11	20	BO	20
21	B11	/BO	21
A12	22	ZO	22
23	B12	/ZO	23
A13	24	DOCOM	24
25	B13	AGND	25
PHOX	26	PHOX	26

Be sure to install the numbers in the correct orientation!!

Pin #1 is on the left side

