

Index

- A**
- Addressing conventions, 21
- B**
- Base register address, 18
 - Baud rate, 15, 18
 - Bezel, 5
- C**
- Cable requirements, 9
 - cables, 10
 - shielded cable, 11
 - Communications Master, 9
 - Connector Specification, 10
 - Programming Cable, 10
 - Connector Specifications, 11
 - PLC-to-Panel Cable, 10
 - Control relays, 22
 - Cutout Area for Panel, 8
- D**
- DCM, 11
 - DCU, 11
 - Decimal numbers, 22
 - Dimensions for Mounting, 8
 - DIP switch, 4
 - DirectSOFT, 2
 - DOS, 15
 - Downloading, 19
- F**
- File number (Allen-Bradley), 18
 - 5/03 and 5/04 (Allen-Bradley), 11
 - Flashing option, 3
- G**
- GE Series 3, 11
- L**
- Labels, 4,5,6
 - Light bars, 12
- M**
- Memory Mapping, 3
- N**
- NEMA, 4
- O**
- Octal numbers, 22
 - OP-9001, 9
 - OP-CMCON-1, 11
 - OP-CMCON-2, 11
 - OPEditor, 2, 15
-

P

Power Supply, 12
power, 12

R

R-memory, 18
Ribbon cable, 9
RS422, 14
pinouts, 10

S

SIMATIC, 11
SLC500, 11
5/03, 11
5/04, 11
Slice I/O, 11
Specification, Storage Temperature, 7
Specifications, 7
communication link, 7
diagnostics, 7
operating humidity, 7
operating temperature, 7
power budget, 7
power connector, 7
weight, 7, 13
System requirements, 15
