



Errata Sheet

This Errata Sheet contains corrections or changes made after the publication of this manual.

Product Family: Productivity 2000

Date: March 13, 2017

Manual Number P2-USER-M

Revision and Date 1st Edition, Rev. C October 2016

Changes to Chapter 2 P2 Specifications

Page 2-67: Corrected weight of module: Correct weight is 97.6 g (3.4 oz); was stated incorrectly as 5g (0.2oz)

P2-08TD1P Sinking Protected DC Output (continued)

General Specifications	
Operating Temperature	0° to 60°C (32° to 140°F)
Storage Temperature	-20° to 70°C (-4° to 158°F)
Humidity	5 to 95% (non-condensing)
Environmental Air	No corrosive gases permitted
Vibration	IEC60068-2-6 (Test Fc)
Shock	IEC60068-2-27 (Test Ea)
Field to Logic Side Isolation	1800VAC applied for 1 second
Insulation Resistance	>10MΩ @ 500VDC
Heat Dissipation	1.8 W
Enclosure Type	Open Equipment
Module Keying to Backplane	Electronic
Module Location	Any I/O slot in any Productivity2000 System.
Field Wiring	Use ZIPLink Wiring System or removable terminal block (not included). See "Wiring Options" in Chapter 5.
EU Directive	See the "EU Directive" topic in the Productivity Suite Help File. Information can also be obtained at: www.productivity2000.com
Connector Type (Sold separately)	18-position removable terminal block
Weight	97.6 g (3.4 oz)
Agency Approvals	UL508 file E139594, Canada & USA CE (EN61131-2*)

* Meets EMC and Safety requirements.



Errata Sheet

Changes to Chapter 2 P2 Specifications

Page 2-13: Updated OLED screens nomenclature. Removed Step 5 on Using Monitor Menu

