



Diffuse sensor - PNP
LTR-M12MA-PMS-603




For use in NFPA 79 Applications only

Sensing range
typ. max. **5...800 mm**

Housing **M12**

Operation range **6...650 mm**



U_b 10...30 VDC
 $I_A \leq 200$ mA

A1: Light-on/IO-Link
 A2: Dark-on

For use in class 2 circuits

Adapters providing field wiring means are available from the manufacturer.
 Refer to manufacturers information.

WARNING - HOT SURFACE - RISK OF BURN - AVERTISSEMENT - SURFACE CHAUDE - RISQUE DE BRÙLURE



CONTRINEX USA
 480 Wrangler Dr 100, Coppel TX 75019 US
 Internet: www.contrinex.com



620-400-283

Made by Contrinex USA

Operators of the products we supply are responsible for compliance with measures for the protection of persons. The use of our equipment in applications where the safety of persons might be at risk is only authorized if the operator observes and implements separate, appropriate and necessary measures for the protection of persons and machines.