CENTER PANEL SUPPORT INSTALLATION

INSTALLATION INSTRUCTIONS

STEP 1: ATTACH RIGHT SUPPORT (ITEM 2) TO LEFT SUPPORT (ITEM 1) AS SHOWN. USE THREE BOLTS, (ITEM 4).

STEP 2: ATTACH TOP/BOTTOM SUPPORT (ITEM 3) TO TOP OF SUPPORT ASSEMBLY AS SHOWN. FASTEN WITH A BOLT (ITEM 4) AND A NUT (ITEM 5).

STEP 3: INSTALL FOUR CHANNEL NUTS (ITEM 6) IN THE CHANNEL PROVIDED IN THE TOP AND BOTTOM OF A 2-DOOR OR 2-DOOR DUAL ACCESS ENCLOSURE.

STEP 4: POSITION CENTER PANEL SUPPORT ASSEMBLY BETWEEN TOP AND BOTTOM MOUNTING CHANNELS IN THE ENCLOSURE. ATTACH CENTER PANEL SUPPORT ASSEMBLY TO MOUNITNG CHANNELS AS SHOWN WITH FOUR BOLTS, (ITEM 4) . LOOSEN BOLT (ITEM 4) TO ADJUST LENGTH OF CENTER PANEL SUPPORT IF REQUIRED.

STEP 5: INSTALL FULL OR HALF PANEL, SWING-OUT PANEL, OR RELAY RACK ANGLES ON THE LEFT SIDE OF CENTER PANEL SUPPORT. SLOTTED HOLES ARE PROVIDED IN TOP SUPPORT (ITEM 3) AND BOTTOM OF LEFT SUPPORT (ITEM 1) TO PROVIDE HORIZONTAL ADJUSTMENT IF REQUIRED.

STEP 6: INSTALL FULL OR HALF PANEL, SWING-OUT PANEL, OR RELAY RACK ANGLES ON RIGHT SIDE OF CENTER PANEL SUPPORT. SLOTTED HOLES ARE PROVIDED IN RIGHT SUPPORT (ITEM 2) TO ADJUST WIDTH OF CENTER PANEL SUPPORT IF REQUIRED.

ITEM #	PART NAME	QTY.
1	SUPPORT, LEFT	1
2	SUPPORT, RIGHT	1
3	SUPPORT TOP/BOTTOM ANGLE	1
102027	BOLT PACK INCLUDES ITEMS 4, 5, 6.	1
4	3/8-16 X 3/4 SERRATED FLANGED BOLT	9
5	3/8-16 X 3/4 SERRATED FLANGED NUT	2
6	3/8-16 CHANNEL NUT	4

SCE-60FSCPS SCE-72FSCPS SCE-90FSCPS

