



(1) Nominal System Voltage Range, Phase to Phase	(2) Limited Approach Boundary - Exposed Movable Conductor		(3) Limited Approach Boundary - Exposed Fixed Circuit Part		(4) Restricted Approach Boundary - Includes Inadvertent Movement Adder	
Less than 50	Not Specified		Not Specified		Not Specified	
50 to 150	10ft 0in	3.0m	3ft 6in	1.0m	Avoid Contact	
151 to 750	10ft 0in	3.0m	3ft 6in	1.0m	1ft 0in	0.3m
751 to 15kV	10ft 0in	3.0m	5ft 0in	1.5m	2ft 2in	0.7m

Approach boundaries are specified in NFPA 70E+ Table 130.4

Hazard Risk Category	Personal Protective Clothing	Personal Protective Equipment
0	Non-Melting, Non-Flammable	Safety Glasses
1	FR Shirt and FR Pants or Coverall	Hard Hat, Safety Glasses, Insulating Glove
2	Cotton Underwear Plus FR Shirt and FR Pants or Coverall	Hard Hat, Safety Glasses, Insulating Glove
3	Cotton Underwear Plus FR Shirt and FR Pants or Coverall	Hard Hat, Flash Suit Hood and Hearing Protection, Insulating Glove
4	Cotton Underwear FR Shirt and FR Pants or Coverall Plus Double Lay Stitching Coat and Pants	Hard Hat, Flash Suit Hood and Hearing Protection, Insulating Glove