

Bellows suction cup (round)

FSGA 43 NBR-55 G1/4-AG

Part no...:10.01.06.00082

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSGA (1.5 Folds) > FSGA 43 NBR-55 G1/4-AG

Bellows suction cup (round) with optimal adaptation to uneven surfaces



Size: 43

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A


Nipple material: Aluminum

Connection: G1/4"-M

Number of folds: 1.5

Vacuum connection: G1/4"-M

Design Data



Attribute	Value
d2	21.90 mm
Dmax(S)	47.50 mm
dn	4.40 mm
Ds	38 mm
G1	G1/4"-M
H	31.60 mm
LG1	11 mm
SW1	17 mm
Z (Stroke)	10 mm

Technical Data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Size	43
Number of folds	1.50
Connection	G1/4-AG
Curve radius (min) (convex)	60 mm
Volume	11.45 cm ³
Suction force (-600mbar)	22.80 N

Bellows suction cup (round)

FSGA 43 NBR-55 G1/4-AG

Part no...:10.01.06.00082

Pull-off force	64.50 N
Hose diameter (empf.) d	6 mm
Weight	19 g
Product family	FSGA

Spare parts



SA-NIP N018 G1/4-AG DN440

Part no...:10.01.06.01065

Nipple family: N 018

Thread G1: G1/4"-M

Length L1: 28.8 mm

Fitting length: 4 mm

Nominal diameter dn: 4.4 mm

Spanner size SW2: 5 mm

Material: Aluminum



FGA 43 NBR-55 N018

Part no...:10.01.06.00131

Size: 43

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Number of folds: 1.5