

## Bellows suction cup (round)

FGA 43 SI-55 N018

Part no...:10.01.06.00127

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FGA 43 SI-55 N018

### Bellows suction cup (round) with optimal adaptation to uneven surfaces




Size: 43

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Number of folds: 1.5

### Design Data



Attribute	Value
d	8 mm
d1	14.50 mm
d2	21.90 mm
D1	45.90 mm
Dk	18 mm
Dmax(S)	47.50 mm
Ds	38 mm
H	27.60 mm
H2	13 mm
H3	17.10 mm
Z (Stroke)	10 mm

### Technical Data


Attribute	Value
Number of folds	1.50
Suction force (-600mbar)	22.80 N
Size	43
Suction cup material	Silicone SI
Weight	11.10 g
Curve radius (min) (convex)	60 mm
Product family	FGA

## Bellows suction cup (round)

FGA 43 SI-55 N018

Part no...:10.01.06.00127

### Accessories



#### SA-NIP N018 G1/4-AG DN440

Part no...:10.01.06.01065

Nipple family: N 018

Thread G1: G1/4"-M

Length L1: 28.8 mm

Fitting length: 4 mm

Nominal diameter dn: 4.4 mm

Spanner size SW2: 5 mm

Material: Aluminum



#### SA-NIP N018 G1/4-IG DN440

Part no...:10.01.06.01066

Nipple family: N 018

Thread G1: G1/4"-F

Length L1: 28.8 mm

Fitting length: 15 mm

Nominal diameter dn: 4.4 mm

Spanner size SW2: 5 mm

Material: Aluminum