

## Bellows suction cup (round)

FGA 14 NBR-55 N016

Part no...:10.01.06.00370

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FGA 14 NBR-55 N016

### Bellows suction cup (round) with optimal adaptation to uneven surfaces




Size: 14

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Number of folds: 1.5

### Design Data



Attribute	Value
d	4.50 mm
d2	5 mm
D1	13.70 mm
Dk	10 mm
Dmax(S)	14.50 mm
Ds	12.50 mm
H	15.50 mm
H2	3.80 mm
H3	8.50 mm
Z (Stroke)	5 mm

### Technical Data

Attribute	Value
Number of folds	1.50
Suction force (-600mbar)	1.20 N
Size	14
Suction cup material	Nitrile rubber NBR
Weight	1.10 g
Curve radius (min) (convex)	12.50 mm
Product family	FGA

## Bellows suction cup (round)

FGA 14 NBR-55 N016

Part no...:10.01.06.00370

### Accessories



#### SA-NIP N016 G1/8-AG DN350

Part no...:10.01.06.05735

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



#### SA-NIP N016 G1/8-IG DN350

Part no...:10.01.06.05731

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18.5 mm

Fitting length: 12 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



#### SA-NIP N016 M5-AG DN250

Part no...:10.01.06.00123

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm


Nominal diameter dn: 2.5 mm

Material: Aluminum

## Bellows suction cup (round)

FGA 14 NBR-55 N016

Part no.:10.01.06.00370



### SPI 14 PEEK

Part no.:10.01.06.03282

Size: 14

Material: Polyetheretherketon