




PNP NO Embeddable


DW-AS-503-P12-624



For use in NFPA 79 Applications only

Housing M12

Operating distance S_n 1.5 mm



U_b 10...30 VDC
 $I_A \leq 200$ mA

For use in class 2 circuits

Max ambiante temperature (IEC 60947-5-2): 100°C

Max temperature according to UL 60947-5-2: 70°C

Adapters providing field wiring means are available from the manufacturer.
Refer to manufacturers information.



CONTRINEX AG Industrial Electronics
Rte du Pâqui 5 - P.O. Box - CH-1720 Corminboeuf - Switzerland

Internet: www.contrinex.com



330-020-197

Made by Contrinex

Operators of the products we supply are responsible for compliance with measures for the protection of persons. The use of our equipment in applications where the safety of persons might be at risk is only authorized if the operator observes and implements separate, appropriate and necessary measures for the protection of persons and machines.