




**NPN NO Non-embeddable**  
**DW-AS-711-M12-967**

For use in NFPA 79 Applications only

Housing **M12**

Operating distance  $S_n$  **3 mm**



$U_b$  10...30 VDC  
 $I_A \leq 200$  mA

For use in class 2 circuits

Max ambiante temperature (IEC 60947-5-2): 85°C  
Max temperature according to UL 60947-5-2: 70°C

Adapters providing field wiring means are available from the manufacturer.  
Refer to manufacturers information.



**CONTRINEX AG** Industrial Electronics  
Rte du Pâqui 5 - P.O. Box - CH-1720 Corminboeuf - Switzerland  
**Internet:** [www.contrinex.com](http://www.contrinex.com)



320-420-758

Made by Contrinex

Operators of the products we supply are responsible for compliance with measures for the protection of persons. The use of our equipment in applications where the safety of persons might be at risk is only authorized if the operator observes and implements separate, appropriate and necessary measures for the protection of persons and machines.