

MR200KG10

Measuring wheel MR200KG10

Circumference 200 mm,

Surface finish: Synthetic (Hytrel, fluted)

Fields of application: Plastic, painted surfaces, paper, pasteboard,  
wood, metal, textiles.For encoder with shaft  $\varnothing$  10 mm.**Product data**

Circumference	200 mm
Surface finish	Synthetic (Hytrel, fluted)
Hardness/Shore A	85 up to 90
Wheel body material	Plastic
Standard bore-hole Width	$\varnothing$ 10 mm
Operating temperature	-10 °C up to +70 °C [+14 °F up to +158 °F]
Weight	35 g
Order number(s)	
MR200KG10	Measuring wheel, bore-hole $\varnothing$ 10 mm

**Drawing MR200KG10**

All dimensional specifications in mm

