

MR200KH10

Measuring wheel MR200KH10

Circumference 200 mm,

Surface finish: Synthetic (Hytrel, even)

Fields of application: Plastic, painted surfaces, paper, pasteboard,
wood, metal, textiles.

For encoder with shaft 10 mm.

**Product data**

| | |
|------------------------|--|
| Circumference | 200 mm |
| Surface finish | Synthetic (Hytrel, even) |
| Hardness/Shore A | 85 up to 90 |
| Wheel body material | Plastic |
| Standard bore-hole | Ø 10 mm |
| Width | 12 mm |
| Operating temperature | -10 °C up to +70 °C [+14 °F up to +158 °F] |
| Weight | 35 g |
| Order number MR200KH10 | Measuring wheel, bore-hole Ø 10 mm |

Drawing MR200KH10

All dimensional specifications in mm

