

**MR500KG10**  
**Measuring wheel MR500KG10**

Circumference 500 mm,  
Surface finish: Synthetic (Hytrel, fluted)  
Fields of application: Plastic, painted surfaces,  
paper, pasteboard, wood, metal, textiles.  
For encoder with shaft  $\varnothing$  10 mm.

**Product data**

Circumference	500 mm
Surface finish	Synthetic (Hytrel, fluted)
Wheel body material	Plastic
Standard bore-hole	$\varnothing$ 10 mm
Width	25 mm
Operating temperature	-10 °C up to +70 °C [+14 °F up to +158 °F]
Weight	260 g
Order number MR500KG10	Measuring wheel, bore-hole $\varnothing$ 10 mm

**Drawing MR500KH10**

All dimensional specifications in mm

