

MR500KH10

Measuring wheel MR500KH10

Circumference 500 mm,

Surface finish: Synthetic (Hytrel, even)

Fields of application: Plastic, painted surfaces, paper,
pasteboard, wood, metal, textiles.For encoder with shaft \varnothing 10 mm.**Product data**

Circumference	500 mm
Surface finish	Synthetic (Hytrel, even)
Hardness/Shore A	85 up to 90
Wheel body material	Plastic
Standard bore-hole	\varnothing 10 mm
Width	25 mm
Operating temperature	-10 °C up to +70 °C [+14 °F up to +158 °F]
Weight	260 g
Order number MR500KH10	Measuring wheel, bore-hole \varnothing 10 mm

Drawing MR500KH10

All dimensional specifications in mm

