

MR500KV

Measuring wheel MR500KV

Circumference 500 mm,

Surface finish: Synthetic (Vulkollan[®], even)Fields of application: Plastic, painted surfaces,
paper, pasteboard, wood, metal, wire.For encoder with shaft \varnothing 10 mm.

Product data

Circumference	500 mm
Surface finish	Synthetic, (Vulkollan [®] , even)
Hardness/Shore A	90 up to 94
Wheel body material	Aluminum
Standard bore-hole	\varnothing 10 mm
Width	25 mm
Operating temperature	-30 °C up to +80 °C [-22 °F up to +176 °F]
Weight	320 g
Order number MR500KV10	Measuring wheel, bore-hole \varnothing 10 mm

Drawing MR500KV

All dimensional specifications in mm

