



WERMA SIGNALTECHNIK **450**

EN 50295: 1999



310.450.001.1011

© D

WERMA
SIGNALTECHNIK

WERMA Signaltechnik GmbH + Co. KG
D-78604 Rietheim-Weilheim
Telefon +49 (0)7424 / 9557-0
Telefax +49 (0)7424 / 9557-44
info@werma.com
www.werma.com


310_450_001_11-10.fm 7.10.11 www.besa-team.de




- ⓐ Anschluss **ausschließlich** durch ausgebildete Elektro-Fachkräfte.
- ⓑ Electrical connection is to be made by trained electrical specialists **only**.
- ⓒ Le branchement doit **uniquement** être effectué par des professionnels.
- ⓓ Il collegamento deve essere eseguito **solo** da elettricisti specializzati.
- ⓔ La conexión **sólo** debe ser realizada por electricistas debidamente formados.
- ⓕ A ligação deve ser feita **exclusivamente** por profissional eléctrico especializado.
- ⓖ Pripojení smí **provádět** pouze kvalifikovaný personál.
- ⓗ Podłączenie **wyłącznie** przez specjalistów-elektryków.
- ⓙ Liittäminen kuuluu **ainoastaan** koulutettujen sähköalan ammattilaisten tehtäviin.
- ⓚ Подключение проводится только специалистами-электриком.
- ⓛ Bağlantı **sadece** eğitimli elektrik teknisyenleri tarafından yapılmalıdır.
- ⓜ 布线需由专业电工执行








IP 65




80 dB



450 x00 55 80 dB (A) / 1 m ~ 2800 Hz
I ≤ 80 mA, I₀ < 500 mA



- ⓐ **Betätigungs- und Reaktionszeiten**
- ⓑ **Activation and reaction times**
- ⓒ **Temps de confirmation et de réaction**





- ① Verdrahtungsbeispiel
- ② Circuit wiring diagram
- ③ Exemple de câblage

