


Port / Contact	M12 contact	Color*
1 - 4 / 1	1	BN
1 - 4 / 3	2	BU
1 / 4	3	WH
2 / 4	4	GN
3 / 4	6	YE
4 / 4	8	GY
1 / 2	5	PK
2 / 2	9	RD
3 / 2	7	BK
4 / 2	10	VT
	11	GY/PK
	12	RD/BU

* when using Murrelektronik cables
 7000-19041-702xxxx
 7000-19041-705xxxx
 7000-19061-702xxxx
 7000-19061-705xxxx



- 1 +24 V ⚡ gn
- 2 S2 ⚡ wh
- 3 0 V
- 4 S1 ⚡ ye



- 1 +24 V
- 2 0 V
- 3 1 / S1
- 4 2 / S1
- 6 3 / S1
- 8 4 / S1
- 5 1 / S2
- 9 2 / S2
- 7 3 / S2
- 10 4 / S2
- 11
- 12

- fastening M4
0,8 Nm -0,2 Nm
- connector M8
0,4 Nm +0,1 Nm
- connector M12
0,6 Nm +0,1 Nm

EN 61984

08.07.09/km/dd