

BRY5262CR



Corrosion Resistant Straight Blade Receptacle.

Product Specifications

Product Type	Receptacle.
Blade Style	Straight Blade.
Device Style	Standard.
Amperage	15A
Voltage	125V
Poles and Wires	2 Pole, 3 Wire.
Receptacle Type	Duplex.
Color	Yellow.
Device Material	Nylon.
Finish	Metal parts have .0003 nickel plating to resist corrosion.
Terminals	Copper-Alloy.
Terminal Screw	Brass combination Phillips/Slotted/Robertson, accepts up to #10 AWG.
Blade/Contact Material	Copper-Alloy.
Mounting/Assembly Screws	Silicon Bronze.
Self Grounding Strap	Copper-Alloy.
Mounting Yoke	Nickel-Plated Brass.
Fed Spec	Verified under #WC596.

UL	UL Listed File #E2258- Guide RTRT.
CSA	CSA Certified File #LR16215- Guide #365E1.
Device Complies With:	NEMA Standards WD-1, WD-6 and UL498.
Overseas Approvals	NOM, CE.
Catalog Page	Click here for catalog page

