


TABLE A

PART NO	LENGTH
G2-RJ12-CBL-2	2.0m (6.6 ft.)



NOTES:

1. UL2464 26AWG*6C+TALCUM
OD: 4.5mm, JACKET BLACK COLOR.
2. RJ12 6P6C MODULAR PLUG.
CONTACT: BRASS, GOLD FLASH.
3. RJ12 6P6C MODULAR PLUG. (圓孔)
CONTACT: BRASS, GOLD FLASH
4. MINIMUM BEND RADIUS - 36mm [1.42 in]
5. OPERATING TEMPERATURE - 0-60°C (32-140°F)

PIN-OUT DIAGRAM



GS-RJ12-CBL-2	
Rev: original	Date: 06/2009
Units: mm [inches]	
Scale: none	
ZIPLINK GS Drive Cable	
