



TABLE A	
PART NO	LENGTH
STP-232HD15-CBL-2	2.0M [6.6FT]



- NOTES:
1. UL20276 28AWG-2P+AEB
OD: 5.0mm, JACKET BLACK COLOR
 2. HD8 15P MALE SOLDERING TYPE
INSULATION: PBT, BLACK COLOR
CONTACT: BRASS, GOLD FLASH
 3. RJ12 6P6C MODULAR PLUG
CONTACT: BRASS, GOLD FLASH
 4. MINIMUM BENDING RADIUS: 40mm [1.57"]
 5. OPERATING TEMPERATURE: 0-60°C (32-140°F)

STP-232HD15-CBL-2	
Rev: A	Date: 06/2012
Units: mm [Inches]	
Scale: none	
ZIPLINK SURE STEP CABLE	
AUTOMATION DIRECT	